

INFRA·SOLID[®]



Data Sheet HISpower

HIS2000R-BWC300

TO-8 Thermal Infrared Emitter


HIS2000R-BWC300

Thermal infrared emitter with Winston cone and BaF₂ window, hermetically sealed


Our HIS2000R-BWC300 is a NiCr filament based thermal emitter in a TO8 package, with a soldered BaF₂ window, filled with N₂ gas. This guarantees hermetically sealed package and long-term stability. The cap with the soldered BaF₂ window is tested with Helium leak test at $< 10^{-8}$ mbar l/s. The gold plated Winston cone collimator bundles and focuses the beam for best optical performance.

HISpower series emitters have an integrated reflector that directs the radiation emitted from the rear to the front through the housing window in order to achieve maximum efficiency. Infrasolid's advanced packaging technology allows soldered sapphire, CaF₂ and BaF₂ windows for use in a wide temperature range of -25 °C up to +85 °C.


Key features



High radiant power



High efficiency



Hermetic housing

- ✓ Pulsable thermal black-body infrared source mounted in an industry standard TO-8 package.
- ✓ Patented nanostructured radiating element achieves up to 500% more detection signal!
- ✓ Lower radiating element temperature of 630 °C increases lifetime!
- ✓ Soldered, high-quality filter windows guarantee considerably less drift. Leakage tested!
- ✓ Wide wavelength range enables a broad range of applications.



*innovative infrared sources for
gas detection & spectroscopy*

Main specifications


Parameter	HIS2000R-BWC300
Package	TO-8
Radiating element area	40 mm ²
Radiating element emissivity	> 0.9
Radiating element temperature	630 °C at 2.5 W
Optical output power	up to 740 mW
Max. electrical power (DC)	2.5 W
Max. electrical voltage	3.8 V
Max. electrical current	660 mA
Electrical resistance	5...6 Ω
Modulation frequency*	4 Hz
Filter/Window	BaF ₂ (soldered)
Wavelength range	2 to 14 μm
Filling gas	N ₂

* 50 % modulation depth, square wave signal, 50 % duty cycle


Optical specifications




Radiating element temperature




Modulation depth




Electrical specifications







Window material transmissivity



HIS2000R-BWC300



Angular radiation distribution



Operating mode recommendation:

All our IR sources can be driven in electrical voltage, current or power regulated mode. The application decides whether the operating mode is DC or AC (pulsed). Depending on the drive mode and the applied electrical power the electrical resistance of the IR emitter can change over time. For highest measurement accuracy a power regulated mode is always recommended for thermal IR emitters. However, it is the most complex operating mode and not suitable in all applications.

For applications that require a small and low-cost driving circuit with a maximum stability we have a technical note with an adjustable low dropout voltage (LDO) regulator.